
VSP004

Accelerometer

VIBRATION SENSOR SUBMERSIBLE





CE CK

Product characteristics			
Measuring range of vibration	[g]	-8080; (-5050 g when connected to a VSE)	
Frequency range	[Hz]	1.512000	
Measuring principle		piezoelectric	
Communication interface		IEPE	
Application			
System		screened cable	
Design		for connection to external diagnostic electronics VSE	
Electrical data			
Bias voltage DC	[V]	1012	
Current consumption	[mA]	0.58	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Reverse polarity protection		yes	
Measuring/setting range			
Measuring range of vibration	[g]	-8080; (-5050 g when connected to a VSE)	
Frequency range	[Hz]	1.512000	
Measuring principle		piezoelectric	
Noise density	[mg]	0.1	
Max. transverse sensitivity	[%]	5	
Minimum measuring time	[s]	2	
Number of measurement		1	
axes			
Accuracy / deviations			
Accuracy		± 10 %	

VSP004

Accelerometer





Measuring sensitivity		100 mV/g			
Interfaces					
Communication interface		IEPE			
Operating conditions					
Ambient temperature	[°C]		-50150		
Storage temperature	[°C]		-2080		
Max. relative air humidity	[%]		80; (50 °C; 50 % non condensing)		
Protection		IP 68; (water-proof up to 100 m 10 bar)			
Tests / approvals					
EMC		EN 61326-1	: 2013		
Shock resistance		EN 61326-1	: 2013		
Mechanical data					
Weight	[g]		1892		
Type of mounting			M8 x 1,25		
Material			housing: stainless steel		
Tightening torque	[Nm]	8			
Remarks					
Pack quantity		1 pcs.			
Electrical connection					
Cable: 25 m, PTFE coated, blue, screened					
white IEPE + black IEPE - screen drain wir	re				