


OBF508



Fibre-optic amplifier

OBF-FAKG/T/AS



Product characteristics		
Type of light	red light	
Housing	rectangular	
Application		
Design	Fibre-optic amplifiers for glass fibre optics, for fibre optics with metal sheath, FE/FT-50	
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Outputs		
Electrical design	PNP/NPN; (automatic load detection PNP/NPN)	
Output function	light-on/dark-on mode; (programmable)	
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed

OBF508



Fibre-optic amplifier

OBF-FAKG/T/AS

Overload protection		yes
Time function	[s]	0.001...0.09
Detection zone		
Range	[m]	0...1; (Through-beam sensor)
Range	[mm]	0...150; (Diffuse reflection sensor)
Factory setting		dark-on mode
Range adjustable		yes
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 65
Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	837
Mechanical data		
Weight	[g]	47.8
Housing		rectangular
Dimensions	[mm]	36 x 15 x 60
Materials		PPE modified
Lens alignment		side lens
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	unsafe zone	1 x LED, red
	excess gain	4 x LED, green
Remarks		
Remarks	light-on mode corresponds to the NC output function for through-beam fibre optics	
	corresponds to the NO output function for diffuse-reflection fibre optics	
	dark-on mode corresponds to the NO output function for through-beam fibre optics	
	corresponds to the NC output function for diffuse-reflection fibre optics	
Pack quantity		1 pcs.

OBF508



Fibre-optic amplifier

OBF-FAKG/TIAS

Electrical connection

Connector: 1 x M8; coding: A

