

Diffuse reflection sensor

OFT-FPKG/6M



Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 30
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	320
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [mm]	1...200; (white paper 200 x 200 mm)
Range adjustable	no
Max. light spot diameter [mm]	92
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

OF5070



Diffuse reflection sensor

OFT-FPKG/6M

MTTF	[years]	891
------	---------	-----

Mechanical data

Weight	[g]	155.2
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 60
Thread designation		M12 x 1
Materials		brass nickel-plated
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Accessories

Items supplied	lock nuts: 2
----------------	--------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PUR; 3 x 0.34 mm²

Connection



BN = Core colours : brown
BU = blue
BK = black



Diffuse reflection sensor

OFT-FPKG/6M

Diagrams and graphs

excess gain graph

