

PF7056



Flush pressure sensor

PF-2,5-RES30-QFPKG/US/ /P

Article no longer available - archive entry

Alternative articles: PF2056
When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
- 2 programming button
- 3 Aseptoflex thread
- 4 Aseptoflex sealing edge



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2
Measuring range [bar]		
Process connection		
		threaded connection Aseptoflex external thread Aseptoflex
Application		
Special feature		Gold-plated contacts
Application		flush mountable for the food and beverage industry
Installation		freely rotatable housing 350°
Media		viscous media and liquids with suspended particles; liquids and gases
Medium temperature [°C]		-25...80
Min. bursting pressure [bar]		50
Pressure rating [bar]		20
Type of pressure		relative pressure
No dead space		yes
Electrical data		
Operating voltage [V]		18...30 DC



Flush pressure sensor

PF-2,5-RES30-QFPKG/US/ /P

Current consumption	[mA]	< 60
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Measuring/setting range

Measuring range	[bar]	0...2.5
Set point SP	[bar]	0.02...2.5
Reset point rP	[bar]	0.01...2.48
In steps of	[bar]	0.01

Accuracy / deviations

Switch point accuracy	[% of the final value]	< ± 1,0
Repeatability	[% of the final value]	< ± 0,25; (with temperature fluctuations < 10 K)
Temperature drift per 10 K		< ± 0.3

Response times

Switching frequency for a given set response time of one output	Response time (dAP)	[ms]	3	6	10	17	30	60	125	250	500
	Switching frequency	[Hz]	170	80	50	30	16	8	4	2	1
Response time	[ms]	at rectangular pressure characteristic; switch point (SPx) = 70 %; reset point (rPx) = 30 %									
Delay time programmable dS, dr	[s]	0, 0,2,...10, 11,...50									

Software / programming

Adjustment of the switch point	programming button
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping

PF7056



Flush pressure sensor

PF-2,5-RES30-QFPKG/US/ /P

Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Materials	stainless steel (316L/1.4404); PBT; PC; EPDM/X; FKM; PA
Materials (wetted parts)	stainless steel (316L/1.4404); ceramics; PTFE
Min. pressure cycles	100 million
Process connection	threaded connection Aseptoflex external thread Aseptoflex

Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

