

SM9004



Magnetic-inductive flow meter

SMR21XGX50KG/US



Product characteristics				
Number of inputs and outputs	Number of analogue outputs: 2			
Measuring range	5...300 l/min	0.3...18 m³/h	80...4755 gph	1.3...79.3 gpm
Process connection	threaded connection G 2 DN50 flat seal			
Application				
Special feature	Gold-plated contacts			
Application	empty pipe detection; for industrial applications			
Installation	connection to pipe by means of an adapter			
Media	conductive liquids; water; hydrous media			



Magnetic-inductive flow meter

SMR21XGX50KG/US

Note on media	conductivity: $\geq 20 \mu\text{S/cm}$	
	viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)	
Medium temperature	-10...80 °C	14...194 °F
Pressure rating [bar]	16	
Pressure rating [MPa]	1.6	
Pressure rating [psi]	232	
MAWP (for applications according to CRN) [bar]	16	

Electrical data		
Operating voltage [V]	18...32 DC; (to SELV/PELV)	
Current consumption [mA]	< 150	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time [s]	5	

Inputs / outputs	
Number of inputs and outputs	Number of analogue outputs: 2

Outputs	
Total number of outputs	2
Output signal	analogue signal
Number of analogue outputs	2
Analogue current output [mA]	4...20; ($\leq 22 \text{ mA}$; scalable)
Max. load [Ω]	500

Measuring/setting range				
Measuring range	5...300 l/min	0.3...18 m³/h	80...4755 gph	1.3...79.3 gpm
Display range	-360...360 l/min	-21.6...21.6 m³/h	-5705...5705 gph	-95.1...95.1 gpm
Resolution	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm
Analogue start point ASP	0...240 l/min	0...14.4 m³/h	0...3800 gph	0...63.4 gpm
Analogue end point AEP	60...300 l/min	3.6...18 m³/h	955...4755 gph	15.9...79.3 gpm
Low flow cut-off LFC	$< 15 \text{ l/min}$	$< 0.9 \text{ m}^3/\text{h}$	$< 240 \text{ gph}$	$< 4 \text{ gpm}$
In steps of	0.5 l/min	0.02 m³/h	5 gph	0.1 gpm
Measuring dynamics	1:60			

Temperature monitoring		
Measuring range	-20...80 °C	-4...176 °F
Display range	-40...100 °C	-40...212 °F
Resolution	0.2 °C	0.5 °F
Analogue start point	-20...60 °C	-4...140 °F
Analogue end point	0...80 °C	32...176 °F
In steps of	0.2 °C	0.5 °F

Accuracy / deviations

Flow monitoring	
Accuracy (in the measuring range)	$\pm (0,8 \% \text{ MW} + 0,5 \% \text{ MEW})$
Repeatability	$\pm 0,2\% \text{ MEW}$

Temperature monitoring	
Temperature drift	$\pm 0,0333 \text{ °C / K}; \pm 0,0599 \text{ °F / K}$



Magnetic-inductive flow meter

SMR21XGX50KG/US

Accuracy	[K]	± 1 (25 °C; Q > 15 l/min) / ± 1 (77 °F; Q > 4 gpm)	
Response times			
Flow monitoring			
Response time	[s]	0.35; (dAP = 0)	
Damping process value dAP	[s]	0...5	
Temperature monitoring			
Dynamic response T05 / T09	[s]	T09 = 3 (Q > 15 l/min) / T09 = 3 (Q > 4 gpm)	
Software / programming			
Parameter setting options		display can be deactivated; Display unit; empty pipe detection	
Operating conditions			
Ambient temperature		-10...60 °C	14...140 °F
Storage temperature		-25...80 °C	-13...176 °F
Protection		IP 65; IP 67	
Tests / approvals			
EMC		DIN EN 60947-5-9	
CPA approval		model number	004MI
		accuracy class	-
		maximum allowable error	± 1,5 % FS
		Q (min)	0,3 m³/h
		Q (t)	-
		Q (max)	18 m³/h
		Medium temperature	-10...70 °C
		Medium temperature	14...158 °F
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	85	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	3050	
Materials		stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEI; FKM; PBT-GF20; TPE-U	
Materials (wetted parts)		stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEEK; Centellen; FKM	
Process connection		threaded connection G 2 DN50 flat seal	
Displays / operating elements			
Display		Display unit	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F)
		function display	1 x LED, yellow (10³)
		measured values	alphanumeric display, 4-digit
		programming	alphanumeric display, 4-digit
Display unit		l/min; m³/h; gpm; gph; °C; °F	
Accessories			
Items supplied		sealings: 2, Centellen	
		Label	
Remarks			
Remarks		MW = measured value	
		MEW = Final value of the measuring range	
Pack quantity		1 pcs.	

SM9004



Magnetic-inductive flow meter

SMR21XGX50KG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1: colours to DIN EN 60947-5-2
analogue output Temperature monitoring
OUT2: analogue output volumetric flow quantity monitoring
Core colours :
BK = black
BN = brown
BU = blue
WH = white



Magnetic-inductive flow meter

SMR21XGX50KG/US


Diagrams and graphs

Pressure loss

dP [mbar] DN50



dP [psi]



dP Pressure loss

Q volumetric flow quantity