




Flow monitor

SCR12ABBAKOW/LS

Article no longer available - archive entry

Alternative articles: SI5006 + E40096
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Number of inputs and outputs	Number of digital outputs: 1
Process connection	G 1/2 external thread
Application	
Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30
Electrical data	
Operating voltage [V]	80...140 AC
Current consumption [mA]	< 40
Power-on delay time [s]	< 20
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 1
Outputs	
Total number of outputs	1
Output signal	switching signal
Number of digital outputs	1
Output function	normally open
Short-circuit protection	no

ST3658



Flow monitor

SCR12ABBAKOW/LS

Overload protection	no
---------------------	----

Measuring/setting range

Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60

Accuracy / deviations

Temperature gradient	[K/min]	15
----------------------	---------	----

Response times

Response time	[s]	1...10
---------------	-----	--------

Software / programming

Adjustment of the switch point	potentiometer
--------------------------------	---------------

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 67

Mechanical data

Materials	PBT-GF20
Materials (wetted parts)	stainless steel (316Ti/1.4571)
Process connection	G 1/2 external thread

Displays / operating elements

Display	function	11 x LED
---------	----------	----------

Accessories


Items supplied	sealings: 2 x AMF 30
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x 1/2"; coding: C



ST3658

Flow monitor

SCR12ABBAKOW/LS



Connection

