



AS-Interface control cabinet module

CabinetModule 4DI 4DO T PW

Article no longer available - archive entry

Alternative articles: AC2709

When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 250
Max. current load total	[A]	0.2
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 4; Number of digital outputs: 4
Inputs		
Number of digital inputs		4; (bidirectional)
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	15...29
Input current High	[mA]	> 3
Input current Low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits		yes
Outputs		
Electrical design		PNP
Number of digital outputs		4
Circuit		PNP
Max. current load per output	[mA]	50
Short-circuit proof		yes
Electrically separated		yes
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 00
Tests / approvals		
EMC		EN 50295
AS-i classification		
AS-i profile		S-7.0
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	0
Mechanical data		
Type of mounting		for Klöckner-Möller housing RMQ16: I 8
Displays / operating elements		
Display	operation	LED, green
	short circuit	LED, red

AC2708



AS-Interface control cabinet module

CabinetModule 4DI 4DO T PW

Remarks	
Remarks	Do not connect any of the following points to an external potential: I-, I+, I1, I2, I3, I4
	The connections are electrically connected with the AS-i cable.
Pack quantity	1 pcs.

Electrical connection

Connection

