


E20767



Sensing head for fibre optic through-beam sensor

FE-11-EPA-M5x30/F1x1



Application	
Function principle	Through-beam sensor
Application	Small bending radius
Detection zone	
Range with fibre-optic amplifier type	OB50; OBF; OO50
OB50	
Range of fibre optics [mm]	175
OBF	
Range of fibre optics [mm]	370
OO50	
Range of fibre optics [mm]	700
Operating conditions	
Ambient temperature [°C]	-40...70
Mechanical data	
Weight [g]	8.2
Version of sensing head	straight
Sensing head thread	M5
Sensing head length [mm]	30
Total length [mm]	wirable
Fibre arrangement	●
Materials	housing: brass white bronze coated
Fibre material	PMMA
Fibre head material	aluminium
Accessories	
Items supplied	hexagon nuts: 4 x M5 washers: 4
Remarks	
Pack quantity	1 pcs.