


# IE5089



## Inductive sensor

IEB3001-BNOG/20m

Article no longer available - archive entry



### Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		III
Reverse polarity protection		no

### Outputs

Electrical design		NPN
Output function		normally closed
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	750
Notes on switching frequency		1000 nb
Short-circuit protection		no
Overload protection		no

### Detection zone

Sensing range	[mm]	1
Real sensing range Sr	[mm]	1 ± 10 %
Operating distance	[mm]	0...0.8

### Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10

### Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

### Tests / approvals

EMC		EN 60947-5-2	class B
		EN 55011	
MTTF	[years]	5515	

# IE5089



## Inductive sensor

IEB3001-BNOG/20m

Mechanical data	
Housing	threaded type
Mounting	flush mountable
Dimensions [mm]	M8 x 1 / L = 35
Thread designation	M8 x 1
Materials	brass white bronze coated; PBT


Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories	
Accessories (supplied)	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

**Electrical connection**  
Cable: 20 m, PVC; 3 x 0.14 mm<sup>2</sup>

### Connection



Core colours :

- BN = brown
- BU = blue
- BK = black

Article no longer available - archive entry