


KI5082



Capacitive sensor

KI-3200NFAKGP2T/US



- 1 LED ring
2 programming buttons



Product characteristics

Electrical design	PNP/NPN; (automatic load detection PNP/NPN)	
Output function	normally open / normally closed; (selectable)	
Sensing range [mm]	20	
Communication interface	IO-Link	
Housing	threaded type	
Dimensions [mm]	M30 x 1.5 / L = 90	

Electrical data

Operating voltage [V]	10..36 DC
Current consumption [mA]	< 20
Protection class	II
Reverse polarity protection	yes
Measuring principle	capacitive

Outputs

Electrical design	PNP/NPN; (automatic load detection PNP/NPN)	
Output function	normally open / normally closed; (selectable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	200	
Switching frequency DC [Hz]	10	
Short-circuit proof	yes	
Overload protection	yes	

Detection zone

Sensing range [mm]	20
--------------------	----

Accuracy / deviations

Hysteresis [% of Sr]	1...15
----------------------	--------

KI5082



Capacitive sensor

KI-3200NFAKGP2T/US



Switch point drift	[% of Sr]	-20...20
Interfaces		
Communication interface		IO-Link
Transmission type		COM 1 (4,8 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Smart Sensor
SIO mode		yes
Min. process cycle time [ms]		101
Supported DeviceIDs	Type of operation	DeviceID
	default	388
Operating conditions		
Ambient temperature [°C]		-25...80
Note on ambient temperature		temperature of the sensing face: -25...110 °C
Protection		IP 65; IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance	EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF [years]		569
Mechanical data		
Weight [g]		88.2
Housing		threaded type
Mounting		non-flush mountable
Dimensions [mm]		M30 x 1.5 / L = 90
Thread designation		M30 x 1.5
Materials	housing: PBT; pushbuttons: TPE-U; LED window: PC	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Teach function		yes
Electronic lock		yes
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.

Capacitive sensor

KI-3200NFAKGP2T/US

Electrical connection - plug

Connector: 1 x M12; coding: A



4:

OUT / IO-Link
automatic load detection PNP/NPN
when using a resistive load < 20 kΩ