

IF0260



Inductive sensor

IFA2002-ABOW/V4A

Article no longer available - archive entry

Alternative articles: IF0292

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally open
Sensing range	[mm]	2
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 71.5

Electrical data

Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC
Protection class		II
Reverse polarity protection		no

Outputs

Output function		normally open
Max. voltage drop switching output AC	[V]	8.5
Minimum load current	[mA]	8
Max. leakage current	[mA]	2
Permanent current rating of switching output AC	[mA]	200; (250 (...50 °C))
Short-time current rating of switching output	[mA]	900; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Short-circuit protection		no
Overload protection		no

Detection zone


Sensing range	[mm]	2
Real sensing range Sr	[mm]	2 ± 10 %
Operating distance	[mm]	0...1.6



Inductive sensor

IFA2002-ABOW/IV4A

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection			IP 67
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		threaded type	
Mounting		flush mountable	
Dimensions		[mm]	M12 x 1 / L = 71.5
Thread designation		M12 x 1	
Materials		stainless steel (1.4571/316Ti); PBT uncoloured	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Cable: 2 m, PVC; 2 x 0.5 mm²			
Connection			



BN = Core colours :
brown
BU = blue