


O7S200



Through-beam sensor transmitter

O7S-OOKG/0,20M/AS



transmitter in upper lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633

Outputs

Switching frequency DC	[Hz]	1000
------------------------	------	------

Detection zone

Transmitter / receiver		transmitter
Range	[m]	0...1.5
Range adjustable		no
Max. light spot diameter	[mm]	90
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	1899

O7S200



Through-beam sensor transmitter

O7S-OOKG/0,20M/AS

Mechanical data		
Weight	[g]	14.2
Housing		rectangular
Dimensions	[mm]	20.3 x 15 x 9
Materials		PA
Lens material		PMMA
Lens alignment		side lens


Displays / operating elements		
Display	operation	1 x LED, green

Remarks		
Remarks	operating voltage "supply class 2" according to UL	
Pack quantity	1 pcs.	

Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm²

Connector: 1 x M8; coding: A; Locking: snap-fit



Connection

