
VKV021

Vibration monitor with intuitive switch point setting

VIBRATION MONITOR



1 Tightening torque 15 Nm
M8 x 1.25 mm

Product characteristics		
Measuring range of vibration	[mm/s]	0...25; (RMS)
Frequency range	[Hz]	10...1000
Application		
Application		vibration monitor to DIN ISO 10816
Electrical data		
Operating voltage	[V]	18...32 DC
Current consumption	[mA]	< 50
Protection class		III
Sensor type		microelectromechanical system (MEMS)
Inputs / outputs		
Total number of inputs and outputs		2
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Outputs		
Output signal		switching signal; analogue signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally closed
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	500
Number of analogue outputs		1
Analogue current output	[mA]	4...20
Max. load	[Ω]	500

VKV021

Vibration monitor with intuitive switch point setting

VIBRATION MONITOR

Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range of vibration [mm/s]		0...25; (RMS)	
Frequency range [Hz]		10...1000	
Number of measurement axes		1	
Accuracy / deviations			
Measuring error [% of the final value]		< ± 3	
Switch point accuracy		< ±4; (% of the final value)	
Repeatability		< 0,5; (% of the final value)	
Linearity deviation		0,25 %	
Response times			
Response time [s]		1...60	
Software / programming			
Adjustment of the switch point		setting ring	
Operating conditions			
Ambient temperature [°C]		-25...80	
Note on ambient temperature		UL application: < 80 °C	
Storage temperature [°C]		-25...80	
Protection		IP 67	
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	10 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
Shock resistance		400 g	
MTTF [years]		510	
Mechanical data			
Weight [g]		113.5	
Type of mounting		M8 x 1,25	
Materials		PBT; PC; FKM; stainless steel (1.4404 / 316L)	
Tightening torque [Nm]		15	
Displays / operating elements			
Display	operation	LED, green	
	switching status	LED, yellow	
With scale		yes	
Operating elements	setting ring	setting ring	
Remarks			
Pack quantity		1 pcs.	

VKV021

Vibration monitor with intuitive switch point setting


VIBRATION MONITOR

Electrical connection

Connector: 1 x M12; coding: A



Connection



1	L+
2	4...20 mA
3	GND
4	switching output