


SM7050



Magnetic-inductive flow meter

SMR34GGX10KG/US-100



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [l/min]	0.2...50
Process connection	threaded connection G 3/4 DN20 flat seal

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Installation	connection to pipe by means of an adapter
Media	conductive liquids; water; hydrous media
Note on media	conductivity: $\geq 20 \mu\text{S/cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)
Medium temperature [°C]	-10...70
Pressure rating [bar]	16
Pressure rating [MPa]	1.6
MAWP (for applications according to CRN) [bar]	11.2

Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	95; (24 V)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	5

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal; IO-Link; (configurable)
Permanent current rating of switching output DC [mA]	250

SM7050



Magnetic-inductive flow meter

SMR34GGX10KG/US-100

Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	500	
Overload protection	yes	
Measuring/setting range		
Measuring range [l/min]	0.2...50	
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)	± (0,8 % MW + 0,5 % MEW)	
Repeatability	± 0,2% MEW	
Response times		
Flow monitoring		
Response time [s]	0.15; (dAP = 0, T19)	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port type	A	
Process data analogue	2	
Min. process cycle time [ms]	3	
Supported DeviceIDs	Type of operation	DeviceID
	default	574
Operating conditions		
Ambient temperature [°C]	-10...60	
Storage temperature [°C]	-25...80	
Protection	IP 67	
Tests / approvals		
EMC	DIN EN 60947-5-9	
CPA approval	model number	001MI
	accuracy class	-
	maximum allowable error	± 1,5 % FS
	Q (min)	0,01 m³/h
	Q (t)	-
	Q (max)	3 m³/h
	Shock resistance	DIN IEC 68-2-27
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF [years]	145	
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight [g]	517.55	

SM7050



Magnetic-inductive flow meter

SMR34GGX10KG/US-100

Materials	stainless steel (316L/1.4404); PBT-GF20; FKM; TPE
Materials (wetted parts)	stainless steel (316L/1.4404); PEEK; FKM
Process connection	threaded connection G 3/4 DN20 flat seal

Remarks


Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



	colours to DIN EN 60947-5-2
OUT1:	IO-Link
OUT2:	analogue output
	Core colours :
BN =	brown
WH =	white
BK =	black
BU =	blue

SM7050


Magnetic-inductive flow meter

SMR34GGX10KG/US-100



Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity