



Inductive sensor

IS-2002-FRKG/4M/PH



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	2
Housing	rectangular
Dimensions [mm]	28 x 10 x 16

Electrical data

Operating voltage [V]	5...36 DC
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10\%$
Operating distance [mm]	0...1.62



Inductive sensor

IS-2002-FRKG/4M/PH

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis [% of Sr]		1...15
Switch point drift [% of Sr]		-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF [years]		2460

Mechanical data

Weight [g]	82
Housing	rectangular
Mounting	flush mountable
Dimensions [mm]	28 x 10 x 16
Materials	PBT
Tightening torque [Nm]	< 0.5; (with washer)

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 4 m, PUR; 2 x 0.14 mm²

Connection



Core colours :
 BK = black
 WH = white