




Through-beam sensor receiver

OUE-DPKG/US-100-DPS



Product characteristics		
Type of light		infrared light
Housing		rectangular
Application		
Function principle		Through-beam sensor
Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880
Outputs		
Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	140
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Transmitter / receiver		receiver
Range	[m]	< 6
Range adjustable		yes
Operating conditions		
Ambient temperature	[°C]	-25...80

OU5046



Through-beam sensor receiver

OUE-DPKG/US-100-DPS

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

MTTF [years]	618
--------------	-----

Mechanical data

Weight [g]	73
------------	----

Housing	rectangular
---------	-------------

Dimensions [mm]	28 x 16 x 51
-----------------	--------------

Materials	PPO modified
-----------	--------------

Lens material	glass
---------------	-------

Lens alignment	side lens
----------------	-----------

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Angle bracket: 1, E20211
----------------	--------------------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection





Through-beam sensor receiver

OUE-DPKG/US-100-DPS

Diagrams and graphs

excess gain graph

