

SF3210




Flow sensor for connection to an evaluation unit

SFR12ABBE0

Article no longer available - archive entry

replaced by: SF311A



Application

Application		Ex zone 0
Medium temperature	[°C]	-20...60
Pressure rating	[bar]	300

Liquids

Application		Ex zone 0
Medium temperature	[°C]	-20...60

Gases

Medium temperature	[°C]	-20...60
--------------------	------	----------

Electrical data

Connection to control monitor		VS 0200 Exi
-------------------------------	--	-------------

Measuring/setting range

Liquids

Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60

Gases

Setting range	[cm/s]	200...2000
Greatest sensitivity	[cm/s]	200...800

Accuracy / deviations

Temperature gradient	[K/min]	15
----------------------	---------	----

Response times

Response time	[s]	1...10
---------------	-----	--------

Liquids

Response time	[s]	1...10
---------------	-----	--------

Gases

Response time	[s]	1...10
---------------	-----	--------

Operating conditions

Protection		IP 67
------------	--	-------

SF3210




Flow sensor for connection to an evaluation unit

SFR12ABBE0

Mechanical data	
Housing	threaded type
Materials	stainless steel (1.4571/316Ti)
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	G 1/2 external thread
Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 2 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm ²	

Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey

Article no longer available - archive entry

replaced by: SF311A