


SMF720



Magnetic-inductive flow meter

SMGX0KGFFRKG/USD



Product characteristics				
Measuring range	50...5000 l/min	3000...300000 l/h	0.1...10 m/s	3...300 m³/h
Nominal diameter	DN100 (4")			
Process connection	ifm-specific device flange			
Application				
Special feature	Gold-plated contacts			
Application	food and beverage industry			
Media	conductive liquids; water; hydrous media			
Note on media	food products such as beer, milk, fruit juices, soft drinks, ketchup, yoghurt, yoghurt toppings, ice cream			
	conductivity: ≥ 5 µS/cm			
Medium temperature	[°C]	-20...150		
Min. bursting pressure	37.5 bar	3.75 MPa		
Pressure rating	25 bar	2.5 MPa		
Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	250; (24V)		
Protection class		III		

SMF720



Magnetic-inductive flow meter

SMGX0KGFFRKG/USD

Reverse polarity protection	yes			
Power-on delay time [s]	< 5			
Measuring principle	magnetic-inductive			
Inputs / outputs				
Total number of inputs and outputs	2			
Inputs				
Inputs	OUT2	external totaliser reset		
Outputs				
Total number of outputs	2			
Output signal	OUT1	pulse signal; totaliser switching signal; diagnostic signal; IO-Link		
	OUT2	analogue signal; pulse signal; totaliser switching signal; diagnostic signal		
Electrical design	PNP/NPN			
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
analogue				
Number of analogue outputs	1			
Analogue current output [mA]	4...20; (skalierbar)			
Max. load [Ω]	500			
Resolution of analogue output	0.38 µA			
Digital				
Number of digital outputs	2			
Max. voltage drop switching output DC [V]	2			
Permanent current rating of switching output DC [mA]	100			
Switching frequency DC [Hz]	0...10000			
Measuring/setting range				
Measuring range	50...5000 l/min	3000...300000 l/h	0.1...10 m/s	3...300 m³/h
Display range	-6000...6000 l/min	-360000...360000 l/h	-12...12 m/s	-360...360 m³/h
Resolution	0.1 l/min	200 l/h	0.01 m/s	0.2 m³/h
Note on factory setting	0...70,0 m³/h			
Analogue start point ASP	0...4000 l/min	0...240000 l/h	0...8.61 m/s	0...240 m³/h
Analogue end point AEP	1000...5000 l/min	60000...300000 l/h	2...10.61 m/s	60...300 m³/h
Low flow cut-off LFC	0...4000 l/min	0...240000 l/h	0...8.61 m/s	0...240 m³/h
Pulse length [s]	0.002...2			
Pulse value	0.001...99990000 l			
Temperature monitoring				
Measuring range [°C]	-20...150			
Display range [°C]	-20...150			
Resolution [°C]	0.01			

SMF720



Magnetic-inductive flow meter

SMGX0KGFFRKG/USD

Analogue start point	[°C]	-20...116
Analogue end point	[°C]	14...150
conductivity monitoring		
Measuring range	[μS/cm]	100...100000
Display range	[μS/cm]	0...100000
Resolution	[μS/cm]	1
Analogue start point	[μS/cm]	0...80000
Analogue end point	[μS/cm]	20000...100000

Accuracy / deviations

volumetric flow monitoring		
Accuracy (in the measuring range)	with optional factory calibration (available from 2025)	± (0,2 % MW + 2 mm/s)
	standard	± (0,5 % MW + 1,5 mm/s)
Repeatability		0,1% MW
Temperature monitoring		
Accuracy	[K]	± 1
Repeatability	[K]	± 0,5
conductivity monitoring		
Accuracy (in the measuring range)	in the range of 100...20000 μS/cm	±10% MW
	in the range of 20000...100000 μS/cm	±20% MW
Repeatability		± 5% MW

Response times

volumetric flow monitoring		
Response time	[s]	< 0.3
Damping process value dAP	[s]	0...5
Temperature monitoring		
Response time	[s]	< 3; (flow velocity: ≥ 0,5m/s)
conductivity monitoring		
Response time	[s]	< 2

Software / programming

Diagnostic functions	direction of flow detection; liquid detection
----------------------	---

Interfaces

Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9	
Profiles	Function class	Designation
	0x4000	Identification and Diagnosis
	0x001B	Measuring and Switching Sensor, floating point, 4 channel
SIO mode	yes	
Required master port type	A	
Process data analogue	6	
Process data binary	8	

SMF720



Magnetic-inductive flow meter

SMGX0KGFFRKG/USD

Min. process cycle time	[ms]	1.9	
IO-Link process data (cyclical)	function	bit length	
	totaliser	32	
	flow	32	
	temperature	32	
	conductivity	32	
	status	4	
	binary switching information	8	
IO-Link functions (acyclical)	direction of flow detection; totaliser; Speicher; operating hours counter; internal temperature; simulation function		
Operating conditions			
Ambient temperature	[°C]	-20...65	
Storage temperature	[°C]	-20...80	
Protection		IP 67; IP 69	
Tests / approvals			
EMC		DIN 61326-1	
Shock resistance		DIN IEC 68-2-27	20 g (18ms)
Vibration resistance		DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF	[years]	81	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	9900	
Inlet pipe length		5 x DN	
Outlet pipe length		2 x DN	
Materials		housing: stainless steel (316L/1.4404); flange: stainless steel (304/1.4301); electronics fixture: stainless steel (304/1.4301); electronics: stainless steel (316L/1.4404); Display: PPSU; Display-Sealing: FKM; LED ring: PP	
Materials (wetted parts)		Pipe section: PFA; electrodes: stainless steel (316L/1.4435)	
Nominal diameter		DN100 (4")	
Process connection		ifm-specific device flange	
Surface characteristics Ra/Rz of the wetted parts		≤ 0.4 µm	
Displays / operating elements			
Factory setting		m³/h; °C; µS/cm	
Display	process value	full graphics TFT display, multi-colour 3,5" 128 x 128 Pixel	
		display layouts: 4	
		display rotation: 4 x 90°	
	operating status	LED ring, three-colour	
Display unit		l/min; l/h; hl/min; hl/h; m³/min; m³/h; m/s; °C; µS/cm; S/m; ms/cm	
Language		German; English; Spanish; French; Italian; Japanese; Korean; Portuguese; Chinese	
Operating elements		4	capacitive pushbuttons

SMF720



Magnetic-inductive flow meter

SMGX0KGFFRKG/USD


Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	reference conditions : water , 15...35 °C, inlet pipe length: 10 x DN, outlet pipe length: 5 x DN
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



1:	L+
2:	OUT2 DO, AO, reset
3:	L-
4:	OUT1 DO, IO-Link