




Temperature cable sensor with process connection

TS-200KCKD10-...../US/

Article no longer available - archive entry

Alternative articles: TS2069

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Measuring range	-40...150 °C	-40...302 °F
Installation length EL [mm]	42	

Application

Special feature	Gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Media	liquids and gases	
Pressure rating [bar]	160	
Note on pressure rating	for mounting in progressive ring fitting	
Minimum installation depth [mm]	15	

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	42	
Measuring range		-40...150 °C	-40...302 °F

Accuracy / deviations

Accuracy [K]	$\pm (0,30 K + 0,005 x t)$
--------------	-----------------------------

Response times

Dynamic response T05 / T09 [s]	6 / 25; (to DIN EN 60751)
--------------------------------	---------------------------

Operating conditions

Ambient temperature [°C]	-25...80
Note on ambient temperature	plug area
Protection	IP 67

Mechanical data

Weight [g]	113.2
Dimensions [mm]	Ø 10
Materials	stainless steel; FKM
Materials (wetted parts)	stainless steel (316L/1.4404)
Probe diameter [mm]	10

TS2051



Temperature cable sensor with process connection

TS-200KCKD10-...../US/

Installation length EL	[mm]	42
------------------------	------	----

Remarks

Remarks	The values for accuracy apply to flowing water.
---------	---

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, FKM

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

